Extraction arms - table mounting



System 50 - Antistatic (AS)

All components RoHS-compatible.

Design:


- · Extraction arm for mounting on table
- Working range 445 1125 mm
- Recommended airflow 45 to 85 m³/h
- · Diameter of tube: Ø50 mm
- Tubes made of chromated TCP Aluminium to assure permanent conductivity
- Joints made of conductive, shatterproof and chemical resistant polypropylene (PP)
- · All O-rings maintenance free and conductive
- Integrated valve. When in an open position out of the flow path to maintain the maximum amount of flow
- · All threaded stays, springs and thumbscrews made of acid-proof stainless steel (AISI 316L)
- All hoods can be provided with a protective netting (accessory) to reduce the risk of extracting foreign objects
- Approved for ESD-areas according to IEC 61340-5-1:2016
- The extraction arms are equipped with an earth wire with a resistance of $1M\Omega$
- · Dismantling of the arm without tools for cleaning

Links: Pressure drop chart, Mounting, User's manual, Capture efficiency, Test reports

Working area

We do not recommend a stationary working position in the upper or lower working area.

All units in mm



A: Model 50-27-1-6

E: Model 50-4737-1-6

Accessory: Extractor Tube no. 1-5021-6

MATRONIC AB 08-556 292 00 Månskärsvägen 10B 14175 Kungens Kurva

